

SPECIFICATION

Product Name : Titan GPS/GALILEO Antenna AA.105

Features : Magnetic Mount Covert stylish design Wide band input voltage Gain can be adjusted for your application (10dB~31dB) IP-67 Waterproof 3M RG174 SMA (M) Straight Cable and connector customizable ROHS Compliant





1. Introduction

Our AA.105 Titan magnetic mount external antenna is ideal for robust, covert installations where durability and small size is paramount. It is used in telematics and M2M applications, for example in commercial vehicle installations for fleet management. It is fully waterproof to IP67 rating. Standard cable and connector version is 3 metre RG174 and SMA(M). Cable length and connector type are customizable upon request.


2. Specifications

ELECTRICAL									
25*25*4mm									
25*25*4mm									
1575.42±3MHz									
10MHz									
1.92 Max									
3dB Typ.									
2dBi Typ.									
50Ω									
RHCP									
LNA									
1575.42MHz									
50Ω									
1.92 Max.									
30dB Typ.									
28.4dB									
2.7~5V									
1.5dB Typ.									
4.7mA @2.7V 6mA @3.3V 10.3mA @5V									
-40°C ~ +85°C									
-40°C ~ +90°C									

*Formula = Patch Antenna Average Gain + LNA typical gain – RG174 cable loss @1.2dB per meter = Gain at connectorGain at the Connector - Patch Gain 2dB + LNA Gain 30dB – Cable loss of 1.2dB per metre (@3m = 3.6dB) = 28.4dB approx.




3. Ceramic Antenna S11 (with housing)





4. Ceramic Antenna Radiation Pattern (with housing)







5. LNA gain

▶REF=0.000 dB	10.000 dB/DIV
<u> </u>	1 : 32,812 df 1 575.420 000 MHz
	P

6. LNA S22






7. Antenna Field Trial Results

Antenna was connected to a U-blox EVK-6H evaluation kit under open sky conditions.


• 1.8 V

Cold Start needs typically 40 seconds.




• 3.3V

Cold Start needs typically 40 seconds.






8. Drawing



RG-174 cable attenuation(dB/100m)												
Frequency(GHz)	0.5	1	1.5	2	2.5	3	3.5	4	4.5	5	5.5	6
Cable Loss(dB)	67	110	127	153	168	183	207	229	252	272	291	311



9. Packaging





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.