RoHS

COMPLIANT

**HALOGEN** 

FREE



# Wirewound, Surface-Mount, Molded, Shielded Inductors

**FEATURES** 



STANDARD ELECTRICAL SPECIFICATIONS								
IND. (μH)	TOL.	TEST FREQ. (MHz) L & Q	Q MIN.	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA) <sup>(1)</sup>		
0.010 0.012 0.015 0.018 0.022 0.027 0.033 0.039 0.047 0.056 0.082 0.10 0.12 0.27 0.33 0.39 0.47 0.56 0.68 0.82 1.0 1.2 1.5 1.5 1.8 2.2 2.7 3.3 3.9 4.7 5.6 6.8 8.2 10.0 12.0 15.0 15.0 15.0 15.0 15.0 15.0 15.0 15	±20%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%%	50 50 50 50 50 50 50 50 50 50 50 25.2 25.2	500 550 555 555 555 555 555 555 555 555	1000 1000 1000 1000 1000 1000 1000 100	0.10 0.11 0.12 0.13 0.15 0.17 0.28 0.35 0.45 0.20 0.20 0.24 0.30 0.33 0.36 0.40 0.48 0.50 0.65 0.75 0.85 0.90 1.10 1.25 1.40 1.60 1.65 2.30 2.70 3.31 3.30 3.31 3.30 3.00	810 750 720 690 640 610 585 530 485 460 630 630 630 630 475 465 450 455 450 455 450 220 210 210 210 210 210 210 210 210 21		

Rated DC current based on the maximum temperature rise, not to exceed 40 °C at +85 °C ambient

- · Molded construction provides superior strength and moisture resistance
- Tape and reel packaging for automatic handling, 2000/reel, EIA-481
- · Compatible with vapor phase, infrared, and wave soldering methods
- Shielded construction minimizes coupling to other components
- · Material categorization: for definitions of compliance please see www.vishav.com/doc?99912


### **ELECTRICAL SPECIFICATIONS**

Inductance range: 0.01 µH to 100 µH Special tolerances available upon request Operating temperature: -55 °C to +125 °C

Coilform material: non-magnetic for 0.01 µH to 0.10 µH;; powdered iron for 0.12 µH to 100 µH

### **TEST EQUIPMENT**

- H/P 4342A Q meter with Vishay Dale test fixture or equivalent
- H/P 4191A RF impedance analyzer (for SRF measurements)
- Wheatstone bridge




Recommended minimum spacing between components

## PART MARKING

- Vishay Dale Inductance code
- Date code

DESCRIPTION								
ISC-1210	10 µH	± 10 %	ER	e3				
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD				



Revision: 10-Sep-2019 Document Number: 34060



# **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.