

Sample &

Buy





#### **OPT8241**

SBAS704B-JUNE 2015-REVISED OCTOBER 2015

Support &

Community

# **OPT8241 3D Time-of-Flight Sensor**

Technical

Documents

# 1 Features

- Imaging Array:
  - 320 × 240 Array
  - 1/3" Optical Format
  - Pixel Pitch: 15 µm
  - Up to 150 Frames per Second
- Optical Properties:
  - Responsivity: 0.35 A/W at 850 nm
  - Demodulation Contrast: 45% at 50 MHz
  - Demodulation Frequency: 10 MHz to 100 MHz
- Output Data Format:
  - 12-Bit Phase Correlation Data
  - 4-Bit Common-Mode (Ambient)
- Chipset Interface:
  - Compatible with TI's Time-of-Flight Controller OPT9221
- Sensor Output Interface:
  - CMOS Data Interface (50-MHz DDR, 16-Lane Data, Clock and Frame Markers)
  - LVDS:
    - 600 Mbps, 3 Data Pairs
    - 1-LVDS Bit Clock Pair, 1-LVDS Sample Clock Pair
- Timing Generator (TG):
  - Addressing Engine with Programmable Region of Interest (ROI)
  - Modulation Control
  - De-Aliasing
  - Master, Slave Sync Operation
- I<sup>2</sup>C Slave Interface for Control
- Power Supply:
  - 3.3-V I/O, Analog
  - 1.8-V Analog, Digital, I/O
  - 1.5-V Demodulation (Typical)
  - Optimized Optical Package (COG-78):
  - 8.757 mm × 7.859 mm × 0.7 mm
  - Integrated Optical Band-Pass Filter (830 nm to 867 nm)
  - Optical Fiducials for Easy Alignment
- Operating Temperature: 0°C to 70°C

# 2 Applications

Tools &

Software

- Depth Sensing:
  - Location and Proximity Sensing

**.**...

- 3D Scanning
- 3D Machine Vision
- Security and Surveillance
- Gesture Controls
- Augmented and Virtual Reality

# **3 Description**

The OPT8241 time-of-flight (ToF) sensor is part of the TI 3D ToF image sensor family. The device combines ToF sensing with an optimally-designed analog-to-digital converter (ADC) and a versatile, programmable timing generator (TG). The device offers quarter video graphics array (QVGA 320 x 240) resolution data at frame rates up to 150 frames per second (600 readouts per second).

The built-in TG controls the reset, modulation, readout, and digitization sequence. The programmability of the TG offers flexibility to optimize for various depth-sensing performance metrics (such as power, motion robustness, signal-to-noise ratio, and ambient cancellation).

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)					
OPT8241	COG (78)	7.859 mm × 8.757 mm					

(1) For all available packages, see the package option addendum at the end of the data sheet.

#### **Block Diagram**



Page

# **Table of Contents**

1	Feat	tures 1					
2	Арр	lications 1					
3	Description 1						
4	Rev	ision History 2					
5	Pin	Configuration and Functions					
6	Spe	cifications					
	6.1	Absolute Maximum Ratings 6					
	6.2	ESD Ratings 6					
	6.3	Recommended Operating Conditions 6					
	6.4	Thermal Information7					
	6.5	Electrical Characteristics7					
	6.6	Timing Requirements 8					
	6.7	Switching Characteristics 8					
	6.8	Optical Characteristics					
	6.9	Typical Characteristics 10					
7	Deta	ailed Description 11					
	7.1	Overview 11					
	7.2	Functional Block Diagram 11					

	7.3	Feature Description	12
	7.4	Device Functional Modes	13
	7.5	Programming	13
8	Appl	ication and Implementation	14
	8.1	Application Information	14
	8.2	Typical Applications	15
9	Pow	er Supply Recommendations	24
10	Layo	out	24
	10.1	Layout Guidelines	24
	10.2	Layout Example	26
	10.3	Mechanical Assembly Guidelines	27
11	Devi	ice and Documentation Support	<mark>28</mark>
	11.1	Documentation Support	28
	11.2	Community Resources	28
	11.3	Trademarks	28
	11.4	Electrostatic Discharge Caution	<mark>28</mark>
	11.5	Glossary	28
12	Мес	hanical, Packaging, and Orderable	
	Infor	mation	<mark>28</mark>

# **4** Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

CI	nanges from Revision A (June 2015) to Revision B	Page
•	Changed equations to correct format throughout document	1
•	Changed name of Function column in Pin Functions table	4
•	Changed SCL and SDATA pin descriptions in Pin Functions table	5
•	Added parameter names to Sensor section of Electrical Characteristics table	7
•	Changed depth resolution description in Table 5	21

### Changes from Original (June 2015) to Revision A

•	aleased to production	1
		•• •



# 5 Pin Configuration and Functions

	Top View (Representative, Not to Scale)																		
	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
A	NC	GPO[0]	SDATA	GND	VMIXH	VMIXH	GND	GND	VMIXH	VMIXH	GND	ILLUM_P	ILLUM_N	DVDDH	GND	ILLUM_ EN	AVDDH	AVDD_ PLL	NC
в	GPO[1]		SCLK														SUB_ BIAS		MCLK
с	VD_IN		RSTZ														NC		DEMOD_ CLK
D	HD_QD		AVDD														RFU		TP2
E	VD_QD		AVSS														PVDD		QPORT
F	VD_FR		REFM														AVSS_ PLL		IOVDD
G	IOVSS		REFP														AVDD		DVSS
н	IOVDD		AVSS														AVSS		DVDD
J	CMOS[14]		VD_SF														TP1		SUM_M
к	CMOS[13]		CMOS[15]														SUM_P		DIFF1_M
L	CMOS[12]		CMOS[11]														DIFF1_P		DCLKM
м	NC	CMOS[10]	CMOS[9]	CMOS[8]	CLKOUT	CMOS[7]	CMOS[6]	CMOS[5]	CMOS[4]	CMOS[3]	CMOS[2]	CMOS[1]	CMOS[0]	PCLK_P	PCLK_M	DIFF0_P	DIFF0_M	DCLKP	NC

NBN Package COG-78 Top View (Representative, Not to Scale)

Texas Instruments

Pin Functions							
	PIN			DESCRIPTION			
NAME	NO.	FUNCTION	I/O BANK	DESCRIPTION			
AVDD	D3, G17	Power	—	1.8-V analog VDD			
AVDD_PLL	A18	Power	—	1.8-V PLL VDD			
AVDDH	A17	Power		3.3-V analog VDD			
AVSS	E3, H3, H17	GND	—	Analog ground			
AVSS_PLL	F17	GND		PLL GND			
CLKOUT	M5	0	IOVDD	Parallel data clock output			
CMOS[0]	M13	0	IOVDD	Parallel data output bit 0			
CMOS[1]	M12	0	IOVDD	Parallel data output bit 1			
CMOS[2]	M11	0	IOVDD	Parallel data output bit 2			
CMOS[3]	M10	0	IOVDD	Parallel data output bit 3			
CMOS[4]	M9	0	IOVDD	Parallel data output bit 4			
CMOS[5]	M8	0	IOVDD	Parallel data output bit 5			
CMOS[6]	M7	0	IOVDD	Parallel data output bit 6			
CMOS[7]	M6	0	IOVDD	Parallel data output bit 7			
CMOS[8]	M4	0	IOVDD	Parallel data output bit 8			
CMOS[9]	M3	0	IOVDD	Parallel data output bit 9			
CMOS[10]	M2	0	IOVDD	Parallel data output bit 10			
CMOS[11]	L3	0	IOVDD	Parallel data output bit 11			
CMOS[12]	L1	0	IOVDD	Parallel data output bit 12			
CMOS[13]	K1	0	IOVDD	Parallel data output bit 13			
CMOS[14]	J1	0	IOVDD	Parallel data output bit 14			
CMOS[15]	K3	0	IOVDD	Parallel data output bit 15			
DCLKM	L19	0	LVDS	Negative LVDS bit clock			
DCLKP	M18	0	LVDS	Positive LVDS bit clock			
DEMOD_CLK	C19	I	IOVDD	Demodulation clock input (optional). This pin has a weak internal pulldown resistor.			
DIFF0_M	M17	0	LVDS	Negative LVDS DIFF0 data pin			
DIFF0_P	M16	0	LVDS	Positive LVDS DIFF0 data pin			
DIFF1_M	K19	0	LVDS	Negative LVDS DIFF1 data pin			
DIFF1_P	L17	0	LVDS	Positive LVDS DIFF1 data pin			
DVDD	H19	Power		1.8-V digital VDD			
DVDDH	A14	Power	_	3.3-V digital VDD			
DVSS	G19	GND	_	Digital GND			
GND	A4, A7, A8, A11, A15	GND	_	Ground			
GPO[0]	A2	0	IOVDD	General-purpose output			
GPO[1]	B1	0	IOVDD	General-purpose output			
HD_QD	D1	0	IOVDD	Quad-frame line sync output			
ILLUM_EN	A16	0	DVDDH	Illumination enable			
ILLUM_N	A13	0	DVDDH	Illumination modulation signal; active low			
ILLUM_P	A12	0	DVDDH	Illumination modulation signal; active high			
IOVDD	H1, F19	Power	_	1.8-V to 3.3-V IOVDD			
IOVSS	G1	GND	_	I/O GND			
MCLK	B19	I	IOVDD	Main clock input for TG. This pin has a weak internal pulldown resistor.			
NC	A1, A19, C17, M1, M19	NC	—	No connection			
PCLK_M	M15	0	LVDS	Negative LVDS pixel clock			



INSTRUMEN

www.ti.com

# Pin Functions (continued)

PIN				DESCRIPTION
NAME	NO.	FUNCTION	I/O BANK	DESCRIPTION
PCLK_P	M14	0	LVDS	Positive LVDS pixel clock
PVDD	E17	Power	—	3.3-V pixel VDD
QPORT	E19	I/O	IOVDD	Debug port. Pullup with an external 1-k $\Omega$ resistor to IOVDD instead.
REFM	F3	Analog In	—	Connect REFM to GND
REFP	G3	Analog Out		ADC reference; connect a 10-nF capacitor close to REFM and REFP.
RFU	D17	RFU	—	Reserved for future use
RSTZ	C3	I	IOVDD	Sensor reset input. This pin has a weak internal pullup resistor.
SCL	B3	I	IOVDD	Clock I <sup>2</sup> C slave interface
SDATA	A3	I/O	IOVDD	Data I <sup>2</sup> C slave interface
SUB_BIAS	B17	Power	—	Substrate bias
SUM_M	J19	0	LVDS	Negative LVDS sum data
SUM_P	K17	0	LVDS	Positive LVDS sum data
TP1	J17	0	—	Debug pin 1, connect to a test pad on the board
TP2	D19	0	—	Debug pin 2, connect to a test pad on the board
VD_FR	F1	0	IOVDD	Frame sync output
VD_IN	C1	I	IOVDD	Frame sync input (optional)
VD_QD	E1	0	IOVDD	Quad-frame sync output
VD_SF	J3	0	—	Sub-frame sync output
VMIXH	A5, A6, A9, A10	Power	_	Mix driver power

# 6 Specifications

## 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
IOVDD	Digital I/O supply	-0.3	4.0	V
AVDDH	Analog supply	-0.3	4.0	V
DVDDH	Digital I/O supply	-0.3	4.0	V
PVDD	Pixel supply	-0.3	4.0	V
AVDD	Analog supply	-0.3	2.2	V
VMIXH	Mix supply	-0.3	2.5	V
DVDD	Digital supply	-0.3	2.2	V
AVDD_PLL	PLL supply	-0.3	2.2	V
VI	Input voltage at input pins	-0.3	VCC + 0.3 <sup>(2)</sup>	V
TJ	Operating junction temperature	0	125	°C
T <sub>stg</sub>	Storage temperature	-40	125	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) VCC refers to the I/O bank voltage.

## 6.2 ESD Ratings

			VALUE	UNIT
V <sub>(ESD)</sub>	Flastraatatia diasharaa	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±1000	V
	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±250	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

# 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
IOVDD	Digital I/O supply	1.7	1.8 to 3.3	3.6	V
AVDDH	Analog supply	3.0	3.3	3.6	V
DVDDH	Digital I/O supply	3.0	3.3	3.6	V
PVDD	Pixel supply	3.0	3.3	3.6	V
AVDD	Analog supply	1.7	1.8	1.9	V
VMIXH	Mix supply	1.4	1.5	2.0	V
DVDD	Digital supply	1.7	1.8	1.9	V
AVDD_PLL	PLL supply	1.7	1.8	1.9	V
T <sub>A</sub>	Operating ambient temperature	0		70	°C

# 6.4 Thermal Information

			OPT8241	
	THERMAL METRIC <sup>(1)</sup>	NBN (COG)	UNIT	
			78 PINS	
D	lunction to empiont thermal resistance	Without underfill	79.2	°C/W
R <sub>0JA</sub>		With underfill	41.0	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance		18.6	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance		51.0	°C/W
Ψյт	Junction-to-top characterization parameter			°C/W
Ψјв	Junction-to-board characterization parame	51.1	°C/W	
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistan	18.6	°C/W	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

# 6.5 Electrical Characteristics

All specifications at  $T_A = 25^{\circ}$ C,  $V_{AVDDH} = 3.3$  V,  $V_{AVDD} = 1.8$  V,  $V_{VMIXH} = 1.5$  V,  $V_{DVDD} = 1.8$  V,  $V_{DVDDH} = 3.3$  V,  $V_{PVDD} = 3.3$  V,  $V_{SUB_BIAS} = 0$  V, integration duty cycle = 10%, system clock frequency = 48 MHz, modulation frequency = 50 MHz, and 850 nm illumination, unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SENSOR						
V	Maximum rows				240	Rows
Н	Maximum columns				320	Columns
P <sub>P</sub>	Pixel pitch			15		μm
POWER (N	lormal Operation)					
I <sub>AVDD_PLL</sub>	PLL supply current			9		mA
	Applog oupply ourrent	Without dynamic power-down		40		m 1
AVDD	Analog supply current	With dynamic power-down		20		ША
I <sub>DVDDH</sub>	3.3-V digital supply current			5		mA
	2.2.) ( opelog oupply ourrept	Without dynamic power-down		17		
AVDDH	3.3-V analog supply current	With dynamic power-down		7		mA
I <sub>PVDD</sub>	Pixel VDD current			2		mA
I <sub>VMIXH</sub>	Demodulation current	10% integration duty cycle		70		٣A
		100% integration duty cycle		600		IIIA
	I/O supply current (CMOS mode)			20		m 1
IOVDD	I/O supply current (LVDS mode)			2		ША
I <sub>DVDD</sub>	Digital supply current			45		mA
POWER (S	standby)					
IIOVDD	I/O supply current			0.7		mA
I <sub>AVDD_PLL</sub>	PLL supply current			0.3		mA
I <sub>AVDD</sub>	Analog supply current			0.3		mA
I <sub>DVDD</sub>	Digital supply current			0.6		mA
IDVDDH	3.3-V digital supply current			1.1		mA
I <sub>AVDDH</sub>	3.3-V analog supply current			0.2		mA
I <sub>VMIXH</sub>	Demodulation current			0		mA
I <sub>PVDD</sub>	Pixel VDD current			0		mA

# **Electrical Characteristics (continued)**

All specifications at  $T_A = 25^{\circ}$ C,  $V_{AVDDH} = 3.3$  V,  $V_{AVDD} = 1.8$  V,  $V_{VMIXH} = 1.5$  V,  $V_{DVDD} = 1.8$  V,  $V_{DVDDH} = 3.3$  V,  $V_{PVDD} = 3.3$  V,  $V_{SUB_BIAS} = 0$  V, integration duty cycle = 10%, system clock frequency = 48 MHz, modulation frequency = 50 MHz, and 850 nm illumination, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP M	X UNIT			
CMOS I/	CMOS I/Os							
V <sub>IH</sub>	Input high-level threshold			0.7 × VCC	<sup>(1)</sup> V			
V <sub>IL</sub>	Input low-level threshold		$0.3 \times VCC^{(1)}$		V			
V	Output high lovel	$I_{OH} = -2 \text{ mA}$	$VCC^{(1)} - 0.45$		V			
VOH	Output high level	$I_{OH} = -8 \text{ mA}$	$VCC^{(1)} - 0.5$		v			
V <sub>OL</sub>		$I_{OL} = 2 \text{ mA}$		0.	35			
	Output Low Level	I <sub>OL</sub> = 8 mA		0.	65 <sup>V</sup>			
		Pins with pullup, pulldown resistor		±	50			
lı	Input pin leakage current	Pins without pullup, pulldown resistor		±	10 <sup>µA</sup>			
CI	Input capacitance				5 pF			
I <sub>OH</sub>	Output ourroot				10			
I <sub>OL</sub>					10 mA			

(1) VCC is equal to IOVDD or DVDDH, based on the I/O bank listed in the *Pin Functions* table.

### 6.6 Timing Requirements

	MIN NO	MAX NAX	UNIT
MCLK duty cycle	48%	52%	
MCLK frequency	12	50	MHz
VD_IN pulse duration	2 × MCLK period		ns
RTSZ low pulse duration (reset)		100	ns

## 6.7 Switching Characteristics

over operating free-air temperature range (unless otherwise noted);  $V_{DVDD} = 1.8 \text{ V}$ ,  $V_{DVDDH} = 3.3 \text{ V}$ , and  $V_{IOVDD} = 1.8 \text{ V}$ 

	PARAMETER	TEST CONDITIONS	MIN	ТҮР	MAX	UNIT		
DDR LVDS MODE								
t <sub>SU</sub>	Data setup time	Data valid to zero crossing of DCLKP, DCLKM		0.48		ns		
t <sub>H</sub>	Data hold time	Zero crossing of DCLKP, DCLKM to data becoming invalid		0.54		ns		
t <sub>FALL</sub> , t <sub>RISE</sub>	Data fall time, data rise time	Rise time measured from -100 mV to +100 mV		0.35		ns		
t <sub>CLKRISE</sub> , t <sub>CLKFALL</sub>	Output clock rise time, output clock fall time	Rise time measured from –100 mV to +100 mV		0.35		ns		
PARALLEL CMOS MODE								
t <sub>SU</sub>	Data setup time	Data valid to zero crossing of CLKOUT		1.5		ns		
t <sub>H</sub>	Data hold time	Zero crossing of CLKOUT to data becoming invalid		3.5		ns		
t <sub>FALL</sub> , t <sub>RISE</sub>	Data fall time, data rise time	Rise time measured from 30% to 70% of IOVDD		2.5		ns		
t <sub>CLKRISE</sub> , t <sub>CLKFALL</sub>	Output clock rise time, output clock fall time	Rise time measured from 30% to 70% of IOVDD		2.2		ns		

# 6.8 Optical Characteristics

over operating free-air temperature range (unless otherwise noted)

		,				
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
	Glass side			Тор		Side
	Passband	0° incident angle	81	3 to 893		nm
	(50% relative transmittance <sup>(1)</sup> )	30° incident angle	79	8 to 877		nm
	Passband	0° incident angle	83	0 to 881		nm
	(90% relative transmittance <sup>(1)</sup> )	30° incident angle	83	8 to 867		nm
AOI	Recommended angle of incidence		0		35	Degrees
	Movimum obsolute transmittenes	0° incident angle	87.34	% at 863		nm
	Maximum absolute transmittance	30° incident angle	81.89	% at 855		nm

(1) Relative transmittance is a ratio of transmittance to maximum absolute transmittance at the same angle of incidence.



(1) Dn = bits D0, D2, D4, and so forth. Dn+1 = bits D1, D3, D5, and so forth.

Figure 1. LVDS Switching Diagram



(2) Dn = bits D0, D1, D2, and so forth.

Figure 2. CMOS Switching Diagram

OPT8241 SBAS704B – JUNE 2015 – REVISED OCTOBER 2015



www.ti.com

# 6.9 Typical Characteristics

At  $V_{AVDDH} = 3.3 \text{ V}$ ,  $V_{AVDD} = 1.8 \text{ V}$ ,  $V_{VMIXH} = 1.5 \text{ V}$ ,  $V_{DVDD} = 1.8 \text{ V}$ ,  $V_{DVDDH} = 3.3 \text{ V}$ ,  $V_{PVDD} = 3.3 \text{ V}$ ,  $V_{SUB_{BIAS}} = 0 \text{ V}$ , and integration duty cycle = 10%, unless otherwise noted.





# 7 Detailed Description

## 7.1 Overview

The OPT8241 is a high-performance quarter video graphics array (QVGA) resolution, 3D sensor device that senses depth information based on the time of flight (ToF) technique. The OPT8241 has a CMOS image sensor core with an integrated analog-to-digital converter (ADC), an addressing engine for the sensor core, an low-voltage differential signaling (LVDS) serializer, and an I<sup>2</sup>C slave device. The device supports configurable timings to optimize power and performance.

The OPT8241 includes the following blocks:

- Timing generator (TG)
- Sensor core
- Addressing engine
- ADC and overload detection
- Modulation block
- Output block
- Temperature sensor
- I<sup>2</sup>C control interface

# 7.2 Functional Block Diagram





#### 7.3 Feature Description

#### 7.3.1 Output Block

The output block provides the output data, clock, and frame boundary signals. The positions of the following frame boundary marker signals are programmable. Table 1 lists signals that can be used by the host processor to reconstruct the frame.

SIGNAL	TYPE	DESCRIPTION
VD_FR	Output	Frame sync
VD_SF	Output	Sub-frame sync
VD_QD	Output	Quad sync
HD_QD	Output	Row sync

#### Table 1. Output Frame Marker Signals

#### 7.3.1.1 Serializer and LVDS Output Interface

The sensor has an option for a serial LVDS interface. The digitized data from the ADCs are serialized and sent on three LVDS data pairs and one LVDS pixel clock pair. The DIFF0, DIFF1 pairs provide the differential data (A-B). The differential data for each pixel is 12 bits long. The pixel clock pair is 0 for the first six data bits and 1 for the next six data bits. The pixel clock can be used by the external host to identify the boundary of the 12-bit data for each pixel. The LVDS waveforms are shown in Figure 6.



Figure 6. LVDS Output Waveforms



#### 7.3.1.2 Parallel CMOS Output Interface

The sensor has options for both serial and parallel data output interfaces. The output data on the parallel CMOS interface toggles on both edges of the clock (DDR rate) with the output clock frequency being equal to the system clock frequency. The CMOS parallel data waveforms are shown in Figure 7.



Figure 7. CMOS Output waveforms

Following the VD start, the first sample set is a frame ID that denotes the quadrant (quad) number. The frame ID format is given in Table 2.

Table 2. Frame ID Word Forma
------------------------------

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
0	1	0	1	0	1	0	1	SF[3:0]			Q[:	3:0]			

Note that Q[3:0] is the quad number and SF[3:0] denotes the sub-frame number.

#### 7.3.2 Temperature Sensor

The on-die temperature sensor can measure temperatures in the range of  $-25^{\circ}$ C to  $125^{\circ}$ C. The temperature is updated every 3 ms. The temperature value is stored in a register that can be read through the l<sup>2</sup>C interface.

#### 7.4 Device Functional Modes

All OPT8241 control commands are directed through the OPT9221 time-of-flight controller. For more details on the functional modes of the chipset, see the OPT9221 datasheet.

# 7.5 Programming

The device registers are programmed by the OPT9221 time-of-flight controller. Therefore, in a typical system, the  $I^2C$  interface is connected to the OPT9221 sensor control  $I^2C$  bus; see the OPT9221 datasheet for more details.

# 8 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 8.1 Application Information

ToF cameras provide the complete depth map of a scene. In contrast with the scanning type light detection and ranging (LIDAR) systems, the depth map of the entire scene is captured at the same instant with an array of ToF pixels. A broad classification of applications for a 3D camera include:

- Presence detection,
- Object location,
- Movement detection, and
- 3D scanning.

The OPT8241 ToF sensor, along with TI's OPT9221 ToF controller, forms a two-chip solution for creating a 3D camera. The block diagram of a complete 3D ToF camera implementation using the OPT8241 is shown in Figure 8.





The TI ToF estimator tool can be used to estimate the performance of a ToF camera with various configurations. The estimator allows control of the following parameters:

- Depth resolution
- 2D resolution (number of pixels)
- Distance range
- Frame rate
- Field of view (FoV)
- Ambient light (in watts x nm x m<sup>2</sup> around the sensor filter bandwidth)
- Reflectivity of the objects

For more details on how to choose the above parameters, see the white paper on the ToF system design.



## 8.2 Typical Applications

#### 8.2.1 Presence Detection for Industrial Safety

Processing 3D information and a separate foreground from the background is computationally less intensive when compared to using color information from a reg, green, blue (RGB) camera. 3D information can also be used to extract the form of the object and classify the object detected as being a human, robot, vehicle, and so forth, as shown in Figure 9.



Figure 9. Industrial Safety

#### 8.2.1.1 Design Requirements

#### **Table 3. Industrial Safety Requirements**

SPECIFICATION	VALUE	UNITS	COMMENTS
Depth resolution	7.5	Percentage of distance	Temporal standard deviation of measured distance without the use of any software filters
Frame rate	30	Frames per second	For reactions fast enough to trigger a machine shut down
Field of view	74.4 × 59.3	Degrees (H × V)	Example only, requirements may vary
Minimum distance	1	Meters	Example only, requirements may vary
Maximum distance	5	Meters	Example only, requirements may vary
Minimum reflectivity of objects at which the depth resolution is specified	40	Percentage	Assuming Lambertian reflection
Number of pixels	320 × 240	Rows x columns	Using a full array
Ambient light	0.1	W × nm × m <sup>2</sup> around 850 nm	Low-intensity diffused sunlight
Illumination source	Laser	—	Laser + diffuser for diffusing light uniformly through the scene

**OPT8241** 

SBAS704B -JUNE 2015-REVISED OCTOBER 2015



#### 8.2.1.2 Detailed Design Procedure

Using the TI ToF estimator tool, the ToF camera design requirements can be input and the power numbers required for achieving the desired specifications can be obtained. The choice of inputs to the estimator tool is explained in the following section.

#### 8.2.1.2.1 Frequencies of Operation

The frequencies of operation are limited by the sensor bandwidth because the illumination source is a laser. Frequencies around 75 MHz can be used to obtain a good demodulation figure of merit. Two frequencies are used to implement de-aliasing and extend the unambiguous range because frequencies around 75 MHz provide a very short unambiguous range. The two frequencies chosen for de-aliasing are 70 MHz and 80 MHz. The unambiguous range is now given by Equation 1.

Unambiguous Range = 
$$\frac{C}{2 \times GCD(f_1, f_2)} = \frac{299792458.0 \text{ ms}}{2 \times GCD(70 \text{ MHz}, 80 \text{ MHz})} = 14.990 \text{ m}$$
 (1)

For the purpose of power requirement calculations, the average frequency of 75 MHz can be used in the estimator tool.

#### 8.2.1.2.2 Number of Sub-Frames and Quads

In this example, two sub-frames and six quads are used to obtain good dynamic range and account for wide ranges of reflectivity and distance. Also, six quads (minimum) are required for implementing de-aliasing. A depth resolution of 5% instead of the requirement of 7.5% is used as the resolution input to the estimator tool to allow for margins resulting from the additional noise when using de-aliasing.

#### 8.2.1.2.3 Field of View (FoV)

Field of view in the horizontal direction is 74.4 degrees. The diagonal FoV can be calculated using Equation 2.

$$FoV(Diagonal) = 2 \times \tan^{-1} \left[ \frac{5}{4} \times \tan\left(\frac{74.4}{2}\right) \right] \approx 87^{\circ}$$
<sup>(2)</sup>

The ratio of 5/4 is used to represent the ratio of the diagonal length to the horizontal length of the sensor.

#### 8.2.1.2.4 Lens

A lens with a 1/3" image circle must be chosen. The FoV of the lens must match the requirements (that is, the FoV must be equal to 87 degrees, as calculated in Equation 2). A lower f.no is always better. For this example, use an f.no of 1.2.

#### 8.2.1.2.5 Integration Duty Cycle

An integration duty cycle of less than 50% is chosen to keep the sensor cool in an industrial housing with no airflow. Choosing an even lower integration duty cycle can result in a marked increase in the peak illumination power. Higher peak illumination power results in a higher number of illumination elements and, thus, an increase in system cost.



#### 8.2.1.2.6 Design Summary

A screen shot of the system estimator tool is shown in Figure 10.

	System Specifications (In	puts)	Design Parameters (Outputs)		
Select Configuration IndustrialSafety	Depth Resolution 250.	000 (mm)	Illum Average Optical Output Power	495.44	(m\)
Add Configuration to Report	Frame Rate 30.0	00 (frames/secor	Illum Peak Optical Output Power	1.98	(W)
Chipset Specifications (Inputs)	Maximum Distance 5.00	0 (m)	X-Y Resolution at Max Distance	23.72	(mm
Sensor OPT8241	Minimum Distance 1.00	0 (m)	Lens Blur at Max Distance	1.75	(mm
Light Source 22045498+Diffuser 🔹			Lens Focal Length	3.16	(mm
Sub-frames 2 (sub-frames/frames/	FoV 87.0	00 (degrees)	Lens Aperture (Aperture Opening)	2.63	(mm
Quads 6 (quads/sub-fram	Minimum F-Numbe 1.20	0 (f/d)	Lens F-Number	1.20	(f/d)
Modulation Frequer75.000 (MHz)	Integration Duty C 50.0	00 (%)	Effective Integration Duty Cycle	50.00	(%)
Pixel Resolution 240 x 320	Reflectivity 40.0	00 (%)	Effective Integration Time/Quad (0.5*Mi	1.39	(ms)
Demod Contrast 26.20 (%)			Max Signal at Min Distance	292.53	(mV
Filter Bandwidth 64.00 (nm)	Ambient Light 0.10	0 (W/nm/m-)	Max Signal at Max Distance	256.28	(mV
Rows 240	Temperature 25.0	00 (°C)	Thermal Noise	709.42	
Columns 320	COC Minimum 100.	000 (mm)	Total Shot Noise	1 51	(m)/
Binning 1	COC Maximum 100	000 (mm)	Sensor Demodulation Power	1.51	(m)A
			Sensor Demodulation Fower	409.00	(IIIW
Tab 1 🛛 Minimur Ma:	imui Number of Ste	+	Depth Resolution vs Distance Across	; reflectivities	
Input 1 None	0	Plot	<u> </u>	/	
Input 2 None 0 0	0	Semilo	g Axis		
Input 3 Object Distance  2 5	10 (m)	📝 Add Plot t	o Rep		
Output Depth Resolution  (mm)					
			10 15 20 25 30 35 Distance(m)	40 45	5.0

### Figure 10. Screen Shot of the Estimator Tool

The illumination peak optical power of 1.98 W can be supplied using one high-power laser.

#### 8.2.1.3 Application Curve







OPT8241 SBAS704B – JUNE 2015 – REVISED OCTOBER 2015



### 8.2.2 People Counting and Locating

Locating and tracking people is a complex problem to solve using regular RGB cameras. With the additional information of distance to each point in the scene, the algorithmic challenges become more surmountable, as shown in Figure 9.



Figure 12. People Counting

## 8.2.2.1 Design Requirements

#### **Table 4. People Counting Requirements**

	-		
SPECIFICATION	VALUE	UNITS	COMMENTS
Depth resolution	200	mm	For basic identification of shapes
Frame rate	15	Frames per second	Reasonable update rate for moderate object movement speeds
Field of view	100.0 × 83.6	Degrees (H × V)	Higher FoVs are better for more coverage but are worse from a power requirement point of view
Minimum distance	1	Meters	Example only, requirements may vary
Maximum distance	6	Meters	Example only, requirements may vary
Typical reflectivity of objects	40	Percentage	Assuming objects reflect very little infrared light and assuming Lambertian reflection.
Number of pixels	320 × 240	Rows × columns	Using a full array
Ambient light	0	W × nm × m <sup>2</sup> around 850 nm	Indoor lighting conditions
Illumination source	LED	—	LED + lens optics



#### 8.2.2.2 Detailed Design Procedure

Using the TI ToF estimator tool, the ToF camera design requirements can be input and the power numbers required for achieving the desired specifications can be obtained by following the procedures discussed in this section.

#### 8.2.2.2.1 Frequencies of Operation

The frequencies of operation are limited by the LED bandwidth because the source of illumination is an LED. Frequencies around 24 MHz can be used to obtain a good demodulation figure of merit if a fast-switching infrared (IR) LED is used. The unambiguous range is given by Equation 3.

Unambiguous Range = 
$$\frac{C}{2 \times f} = \frac{299792458.0 \text{ ms}}{2 \times 24 \text{ MHz}} = 6.246 \text{ m}$$
 (3)

#### 8.2.2.2.2 Number of Sub-Frames and Quads

In this example, one sub-frame and four quads are used to minimize the effects of the sensor reset noise.

#### 8.2.2.2.3 Field of View (FoV)

Field of view in the horizontal direction is 74.4 degrees. The diagonal field of view can be calculated using Equation 2.

$$FoV(Diagonal) = 2 \times \tan^{-1} \left[ \frac{5}{4} \times \tan\left(\frac{100.0}{2}\right) \right] \approx 112.3^{\circ}$$
(4)

The ratio of 5/4 is used to represent the ratio of the diagonal length to the horizontal length of the sensor.

#### 8.2.2.2.4 Lens

A lens with a 1/3" image circle must be chosen. The field of view of the lens must match the requirements (that is, the FoV must be equal to 112.3 degrees, as calculated in Equation 4). A lower f.no is always better. For this example, use an f.no of 1.2.

#### 8.2.2.2.5 Integration Duty Cycle

An integration duty cycle of 60% is chosen to keep the peak illumination power requirements low. Higher peak illumination power results in a higher number of illumination elements and, thus, an increase in system cost.

**OPT8241** 

SBAS704B -JUNE 2015-REVISED OCTOBER 2015



#### 8.2.2.2.6 Design Summary

A screen shot of the system estimator tool is shown in Figure 13.

	- System Specification	ons (Inputs)	Design Parameters (Outputs)	
Select Configuration PeopleCounting	Depth Resolution	200.000 (mm)	Illum Average Optical Output Power	605.90 (mW
Add Configuration to Report	Frame Rate	15.000 (frames/secor	Illum Peak Optical Output Power	2.02 (W)
Chipset Specifications (Inputs)	Maximum Distan	c€ 6.000 (m)	X-Y Resolution at Max Distance	44.73 (mm
Sensor OPT8241   Light Source SFH4232	Minimum Distanc	ce 1.000 (m)	Lens Blur at Max Distance Lens Focal Length	1.20 (mm 2.01 (mm
Sub-frames 1 (sub-frames/frar	FoV	112.300 (degrees)	Lens Aperture (Aperture Opening)	1.68 (mm
Quads 4 (quads/sub-fram	Minimum F-Num	be 1.200 (f/d)	Lens F-Number	1.20 (f/d)
Modulation Frequer 24.000 (MHz)	Integration Duty	C 60.000 (%)	Effective Integration Duty Cycle	60.00 (%)
Pixel Resolution 240 x 320 Demod Contrast 40.80 (%)	Reflectivity	40.000 (%)	Effective Integration Time/Quad (0.5*Mi	10.00 (ms)
Filter Bandwidth 64.00 (nm)	Ambient Light	0.000 (W/nm/m <sup>2</sup> )	Max Signal at Min Distance	125.36 (mV
RoI+Binning Rows 240	Temperature	25.000 (°C)	Max Signal at Max Distance	3.48 (mV
Columns 320	COC Minimum	100.000 (mm)	Total Shot Noise	798.42 (uV)
Binning 1	COC Maximum	100.000 (mm)	Sensor Demodulation Power	587.52 (mW
( Tab 1 🛛		+	200 Depth Resolution vs Distance Across	reflectivities
Minimur Maxi	mui Number of Ste		E <sup>30</sup> 100%	
Input 1 None    O  0  0	0	Plot		
Input 2 None 0 0	0	Semilog	Axis	
Input 3 Object Distance 1 6	100	(m) 📝 Add Plot to	Rep	
Output Depth Resolution   (mm)				5 6
			Distance(m)	5 6

Figure 13. Screen Shot of the Estimator Tool

The illumination peak optical power of 2.0 W can be supplied using a single high-power LED.

#### 8.2.2.3 Application Curve



p represents object reflectivity

Figure 14. Example People-Counting Object Distance vs Depth Resolution



#### 8.2.3 People Locating and Identification

A skeletal structure can be used to classify identified shapes (such as humans, machines, pets, and so forth). Other possibilities include classification of people (such as children and elderly). Even identification of humans by matching the shape and movement to an existing database is possible. Such information can lend itself for use in a variety of retail solutions, home safety, security, and public and private surveillance systems, as shown in Figure 15.



Figure 15. People Counting and Identification

# 8.2.3.1 Design Requirements

SPECIFICATION	VALUE	UNITS	COMMENTS		
Depth resolution	1.5	Percentage of distance	To obtain skeletal structure and gait accurately and identify humans from other objects.		
Frame rate	15	Frame per second	Reasonable update rate for moderate object movement speeds		
Field of view	100.0 x 83.6	Degrees (H X V)	Higher FoVs are better for more coverage but worse from a power requirement point of view		
Minimum distance	1	Meters	Example only, requirements may vary		
Maximum distance	6	Meters	Example only, requirements may vary		
Typical reflectivity of objects	40	Percentage	Assuming objects reflect very little infrared light and assuming Lambertian reflection		
No of pixels	320 x 240	Rows x columns	Using full array		
Ambient light	0	W × nm × m <sup>2</sup> around 850 nm	Indoor lighting conditions		
Illumination source	Laser	_	Laser + diffuser for diffusing light uniformly through the scene		



#### 8.2.3.2 Detailed Design Procedure

Using the TI ToF estimator tool, the ToF camera design requirements can be input and the power numbers required for achieving the desired specifications can be obtained. The choice of inputs to the estimator tool is explained in the following section.

#### 8.2.3.2.1 Frequencies of Operation

The frequencies of operation are limited by the sensor bandwidth because the illumination source is a laser. Frequencies around 75 MHz can be used to obtain a good demodulation figure of merit. Two frequencies are used to implement de-aliasing and extend the unambiguous range because frequencies around 75 MHz provide a very short unambiguous range. The two frequencies chosen for de-aliasing are 70 MHz and 80 MHz. The unambiguous range is now given by Equation 5.

Unambiguous Range = 
$$\frac{C}{2 \times GCD(f_1, f_2)} = \frac{299792458.0 \text{ ms}}{2 \times GCD(70 \text{ MHz}, 80 \text{ MHz})} = 14.990 \text{ m}$$
 (5)

For the purpose of power requirement calculations, the average frequency of 75 MHz can be used in the estimator tool.

#### 8.2.3.2.2 Number of Sub-Frames and Quads

In this example, one sub-frame and six quads are used to minimize the effects of the sensor reset noise. A depth resolution of 1% instead of the requirement of 1.5% is used as the resolution input to the estimator tool to allow for margins resulting from the additional noise when using de-aliasing.

### 8.2.3.2.3 Field of View (FoV)

Field of view in the horizontal direction is 74.4 degrees. The diagonal FoV can be calculated using Equation 6.

$$FoV(Diagonal) = 2 \times \tan^{-1} \left[ \frac{5}{4} \times \tan \left( \frac{100.0}{2} \right) \right] \approx 112.3^{\circ}$$
(6)

The ratio of 5/4 is used to represent the ratio of the diagonal length to the horizontal length of the sensor.

#### 8.2.3.2.4 Lens

A lens with a 1/3" image circle must be chosen. The FoV of the lens must match the requirements (that is, the FoV must be equal to 112.3 degrees, as calculated in Equation 6). A lower f.no is always better. For this example, use an f.no of 1.2.

#### 8.2.3.2.5 Integration Duty Cycle

An integration duty cycle of 70% is chosen to keep the peak illumination power requirements low. Higher peak illumination power results in a higher number of illumination elements and, thus, an increase in system cost.



#### 8.2.3.2.6 Design Summary

A screen shot of the system estimator tool is shown in Figure 16.

	System Specifications	s (Inputs)	Design Parameters (Outputs)			
Select Configuration PeopleIdentification -	Depth Resolution	60.000 (mm)	Illum Average Optical Output Power	1.24 (W)		
Add Configuration to Report	Frame Rate	15.000 (frames/secor	Illum Peak Optical Output Power	3.54 (W)		
Chipset Specifications (Inputs) Sensor OPT8241  Light Source 22045498+Diffuser  Sub-frames 1 (sub-frames/frar Quads 6 (quads/sub-fram Modulation Frequei 75.000 (MHz) Pixel Resolution 240 x 320 Demod Contrast 26.20 (%) Filter Bandwidth 64.00 (nm) Rol+Binning	Maximum Distance Minimum Distance FoV Minimum F-Numbe Integration Duty C Reflectivity Ambient Light	6.000 (m) 1.000 (m) 112.300 (degrees) 1.200 (f/d) 70 (%) 40.000 (%) 0.000 (W/nm/m <sup>2</sup> )	X-Y Resolution at Max Distance Lens Blur at Max Distance Lens Focal Length Lens Aperture (Aperture Opening) Lens F-Number Effective Integration Duty Cycle Effective Integration Time/Quad (0.5*Mi Max Signal at Min Distance Max Signal at Max Distance	44.73     (mm       1.20     (mm       2.01     (mm       1.68     (mm       1.20     (f/d)       70.00     (%)       7.78     (ms)       153.31     (mV       4.26     (mV		
Rows240Columns320Binning1	Temperature COC Minimum COC Maximum	25.000 (°C) 100.000 (mm) 100.000 (mm)	Thermal Noise Total Shot Noise Sensor Demodulation Power	798.42 (uV) 173.31 (uV) 685.44 (mW		
Tab 1     Minimur     Maxi       Input 1     None     0     0       Input 2     None     0     0       Input 3     Object Distance     1     6       Output     Depth Resolution     (mm)	imui Number of Ste 0 0 100 (1	+ Plot Semilog J m) V Add Plot to I	Axis Rep	reflectivities		

Figure 16. Screen Shot of the Estimator Tool

The illumination peak optical power of 3.54 W can be supplied using two high-power lasers.

#### 8.2.3.3 Application Curve



ρ represents object reflectivity

Figure 17. Example People Identification Object Distance vs Depth Resolution



# 9 Power Supply Recommendations

The sensor reset noise is sensitive to AVDDH and PVDD supplies. Therefore, linear regulators are recommended for supplying power to the AVDD and PVDD supplies. DC-DC regulators can be used to supply power to the rest of the supplies. Ripple voltage on the VMIX and the SUB\_BIAS supplies must be kept at a minimum (< 50 mV) to minimize phase noise resulting from differences between quads. The VMIX regulator must have the bandwidth to supply surge current requirements within a short time of less than 10  $\mu$ s after the integration period begins because VMIX currents have a pulsed profile.

There is no strict order for the power-on or -off sequence. The VMIX supplies are recommended to be turned on after all supplies have ramped to 90% of their respective values to avoid any power-up surges resulting from high VMIX currents in a non-reset device state.

# 10 Layout

## 10.1 Layout Guidelines

### 10.1.1 MIX Supply Decapacitors

The VMIXH supply has a peak load current requirement of approximately 600 mA during the integration phase. Moreover, a break-before-make circuit is used during the reversal of the demodulation polarity to avoid high through currents. The break-before-make strategy results in a pulse with a drop and a subsequent rise of demodulation current. The pulse duration is typically approximately 1 ns. In order to effectively support the rise in currents, VMIXH decoupling capacitors must be placed very close to the package. Furthermore, use multiple capacitors to reduce the effect of equivalent series inductance and resistance of the decoupling capacitors. Use a combination of 10-nF and 1-nF capacitors per VMIXH pin. Using vias for routing the trace from decoupling capacitors to the package pins must be avoided.

### 10.1.2 LVDS Transmitters

Each LVDS data output pair must be routed as a 100- $\Omega$  differential pair. When used with the OPT9221, 100- $\Omega$  termination resistors must be placed close to the OPT9221.

#### 10.1.3 Optical Centering

The lens mount placement on the printed circuit board (PCB) must be such that the lens optical center aligns with the pixel array optical center. Note that the pixel array center is different from the package center.



### Layout Guidelines (continued)

# 10.1.4 Image Orientation

The sensor orientation for obtaining an upright image is shown in Figure 18.



the default sensor readout direction is shown in grey.

### Figure 18. Sensor Orientation for Obtaining an Upright Image

#### **10.1.5** Thermal Considerations

In some applications, special care must be taken to avoid high sensor temperatures because demodulation power is considerably high for the size of the package. Lower sensor temperatures help lower the thermal noise floor as well as reduce the leakage currents. Two recommended methods for achieving better package to PCB thermal coupling are listed below:

- Use a thermal pad below the sensor on both sides of the PCB with stitched vias.
- Use a compatible underfill.

OPT8241 SBAS704B-JUNE 2015-REVISED OCTOBER 2015



www.ti.com

# 10.2 Layout Example



Figure 19. Example Layout



### **10.3 Mechanical Assembly Guidelines**

#### 10.3.1 Board-Level Reliability

TI chip-on-glass products are designed and tested with underfill to ensure excellent board-level reliability in intended applications. If a customer chooses to underfill a chip-on-glass product, following the guidelines below is recommended to maximize the board level reliability:

- The underfill material must extend partially up the package edges. Underfill that ends at the bottom (ball side) of the die degrades reliability.
- The underfill material must have a coefficient of thermal expansion (CTE) closely matched to the CTE of the solder interconnect.
- The underfill material must have a glass transition temperature (Tg) above the expected maximum exposure temperature.

Thermoset ME-525 is a good example of a compatible underfill.

### 10.3.2 Handling

To avoid dust particles on the sensor, the sensor tray must only be opened in a cleanroom facility. In case of accidental exposure to dust, the recommended method to clean the sensors is to use an IPA solution with a micro-fiber cloth swab with no lint. Do not handle the sensor edges with hard or abrasive materials (such as metal tweezers) because the sensor package has a glass outline. Such handling may lead to cracks that can negatively affect package reliability and image quality.

TEXAS INSTRUMENTS

www.ti.com

# **11** Device and Documentation Support

### **11.1 Documentation Support**

#### 11.1.1 Related Documentation

OPT9221 Data Sheet, SBAS703

Introduction to the Time-of-Flight (ToF) System Design, SBAU219

### **11.2 Community Resources**

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 11.3 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

#### **11.4 Electrostatic Discharge Caution**



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 11.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



10-Dec-2020

# PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
OPT8241NBN	ACTIVE	COG	NBN	78	240	RoHS & Green	SNAGCU	Level-3-260C-168 HR	0 to 70	OPT8241	Samples
OPT8241NBNL	ACTIVE	COG	NBN	78	2400	RoHS & Green	SNAGCU	Level-3-260C-168 HR	0 to 70	OPT8241	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# PACKAGE OPTION ADDENDUM

10-Dec-2020

# **NBN0078A**



# PACKAGE OUTLINE

# COG - 0.745 mm max height

CHIP ON GLASS



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. Dimension is measured at the maximum solder ball diameter, parallel to primary datum C.
- 4. Primary datum C and seating plane are defined by the spherical crowns of the solder balls.



# **NBN0078A**

# **EXAMPLE BOARD LAYOUT**

# COG - 0.745 mm max height

CHIP ON GLASS



NOTES: (continued)

5. PCB pads shift from original positions to prevent solder balls from touching sensor. X and Y direction: 0.05 mm. Corner pads: 0.03 mm.

6. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.

For information, see Texas Instruments literature number SSYZ015 (www.ti.com/lit/ssyz015).



# **NBN0078A**

# **EXAMPLE STENCIL DESIGN**

# COG - 0.745 mm max height

CHIP ON GLASS



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated