
SDLS123 - MARCH 1974 - REVISED MARCH 1988

| | TYPICAL | TYPICAL |
|--------------|-------------|---------------|
| TYPE | POWER | DELAY |
| | DISSIPATION | (4-BIT WORDS) |
| '85 | 275 mW | 23 ns |
| LS85 | 52 mW | 24 ns |
| ' S85 | 365 mW | 11 ns |


description

These four-bit magnitude comparators perform comparison of straight binary and straight BCD (8-4-2-1) codes. Three fully decoded decisions about two 4-bit words (A, B) are made and are externally available at three outputs. These devices are fully expandable to any number of bits without external gates. Words of greater length may be compared by connecting comparators in cascade. The A > B, A < B, and A = B outputs of a stage handling less-significant bits are connected to the corresponding A > B, A < B, and A = B inputs of the next stage handling more-significant bits. The stage handling the least-significant bits must have a high-level voltage applied to the A = B input. The cascading paths of the '85, 'LS85, and 'S85 are implemented with only a two-gate-level delay to reduce overall comparison times for long words. An alternate method of cascading which further reduces the comparison time is shown in the typical application data.

SN5485, SN54LS85, SN54S85 . . . J OR W PACKAGE SN7485 : . . N PACKAGE SN74LS85, SN74S85 . . . D OR N PACKAGE (TOP VIEW)



SN54LS85, SN54S85 . . . FK PACKAGE (TOP VIEW)




NC - No internal connection


FUNCTION TABLE

| | COMP | ARING UTS | | | CASCADING INPUTS | | | OUTPUTS | |
|---------|---------|--------------|---------|-------|---------------------|-------|-------|---------|-------|
| A3, B3 | A2, B2 | A1, B1 | A0, B0 | A > B | A < B | A = B | A > B | A < B | A = 8 |
| A3 > B3 | X | × | × | × | Х | × | Н | L | L |
| A3 < B3 | × | × | × | × | X | × | L | н | L |
| A3 = B3 | A2 > B2 | × | × | × | X | × | н | L | L |
| A3 = B3 | A2 < B2 | × | × | × | X | × | L | Н | L |
| A3 = B2 | A2 = B2 | A1 > B1 | × | × | X | × | н | L | L |
| A3 = B3 | A2 = B2 | A1 < B1 | × | × | X | × | L | н | L |
| A2 = B3 | A2 = B2 | A1 = B1 | A0 > B0 | × | X | × | н | L | L |
| A3 = B3 | A2 = B2 | A1 = B1 | A0 < B0 | × | Х | × | L | Н | L |
| A3 = B3 | A2 = B2 | A1 = B1 | A0 = B0 | н | L | L | Н | L | L |
| A3 = B3 | A2 = B2 | A1 = B1 | AO = BO | L | H | L | L | Н | L |
| A3 = B3 | A2 = B2 | A1 = B1 | A0 = B0 | × | X | Н | L | L | Н |
| A3 = B3 | A2 = B2 | A1 = B1 | AO = BO | н | н | Ł | L | L | L |
| A3 = B3 | A2 = B2 | A1 = B1 | A0 = B0 | L | L _ | L | н | Н | L |

logic diagrams (positive logic)




logic symbol†





†This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12. Pin numbers shown are for D, J, N, and W packages.




schematics of inputs and outputs









absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

| | SN54' SN54S' | SN54LS' | SN74' SN74S' | SN74LS' | UNIT |
|--|-----------------|---------|-----------------|---------|------|
| Supply voltage, V _{CC} (see Note 1) | 7 | 7 | 7 | 7 | V |
| Input voltage | 5.5 | 7 | 5.5 | 7 | V |
| Interemitter voltage (see Note 2) | 5.5 | | 5.5 | | V |
| Operating free-air temperature range | - 55 | to 125 | -0 | to 70 | °C |
| Storage temperature range | - 65 | to 150 | - 65 | to 150 | °C |

NOTES: 1. Voltage values, except interemitter voltage, are with respect to network ground terminal.

2. This is the voltage between two emitters of a multiple-emitter input transistor. This rating applies to each A input in conjunction with its respective B input of the '85 and 'S85.



SN5485, SN54LS85, SN54S85 SN7485, SN74LS85, SN74S85 4-BIT MAGNITUDE COMPARATORS

SDLS123 - MARCH 1974 - REVISED MARCH 1988

recommended operating conditions

| | | SN5485 | 5 | | SN7485 | | |
|------------------------------------|-----|--------|------|------|--------|------|------|
| | MIN | NOM | MAX | MIN | NOM | MAX | UNIT |
| Supply voltage, V _{CC} | 4.5 | 5 | 5.5 | 4.75 | 5 | 5.25 | ٧ |
| High-level output current, IOH | | | -400 | | | -400 | μΑ |
| Low-level output current, IOL | | | 16 | | | 16 | mA |
| Operating free-air temperature, TA | -55 | | 125 | 0 | | 70 | °C |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | PARAMETER | | TE | ST CONDITI | ONS† | | MIN | TYP‡ | MAX | UNIT |
|-----|--|---------------------|--|------------|-------------------------|-----------------|-----|------|------|------|
| VIH | High-level input voltage | | | | | | 2 | | | V |
| VIL | Low-level input voltage | | | | | | | | 0.8 | ٧ |
| VIK | Input clamp voltage | | V _{CC} = MIN, | | I _I = -12 mA | | | | -1.5 | V |
| Vон | High-level output voltage | | V _{CC} = MIN, V _{IL} = 0.8 V, | | V _{IH} = 2 | 2 ∨, -400 μA | 2.4 | 3.4 | | ٧ |
| VOL | Low-level output voltage | | V _{CC} = MIN, V _{IL} = 0.8 V, | | V _{IH} = 2 | | | 0.2 | 0.4 | ٧ |
| Ч | Input current at maximum in | nput voltage | V _{CC} = MAX, | | V _I = 5. | 5 V | | | 1 | mA |
| 1 | Mich level in the survey of th | A < B, A > B inputs | V 440 V | | 14 - 2 | 4.17 | | | 40 | |
| ΉН | High-level input current | all other inputs | V _{CC} = MAX, | | V ₁ = 2.4 | + V | | | 120 | μΑ |
| 1 | Law law Line Annual | A < B, A > B inputs | V - MAY | | · · · · · | 4.17 | | | -1.6 | |
| HE | Low-level input current | all other inputs | V _{CC} = MAX, | | V ₁ = 0.4 | 4 V | | | -4.8 | mA |
| | | 2 | ., | | | SN5485 | -20 | | -55 | |
| los | Short-circuit output current | 3 | V _{CC} = MAX, | v0 = 0 | | SN7485 | -18 | | -55 | mA |
| 1cc | Supply current | | V _{CC} = MAX, | See Note 4 | | | | 55 | 88 | mA |

 $^{^\}dagger$ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

NOTE 4: I_{CC} is measured with outputs open, A = B grounded, and all other inputs at 4.5 V.

switching characteristics, VCC = 5 V, TA = 25°C

| PARAMETER | FROM INPUT | TO OUTPUT | NUMBER OF GATE LEVELS | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-------------------|-----------------------|----------------|--------------------------|-------------------------|-----|-----|-----|------|
| | | · | 1 | | | 7 | | |
| | A A B - | A < B, $A > B$ | 2 | | | 12 | | |
| ^t PLH | Any A or B data input | | 3 |] | | 17 | 26 | ns |
| | | A = B | 4 |] | | 23 | 35 | |
| | | | 1 | | | 11 | | |
| | | A < B, A > B | 2 | C _L = 15 pF, | | 15 | | |
| ^t PH L | Any A or B data input | , | 3 | $R_1 = 400 \Omega$ | | 20 | 30 | ns |
| | | A = B | 4 | See Note 5 | | 20 | 30 | |
| tPLH | A < B or A = B | A > B | 1 | See Note 5 | | 7 | 11 | ns |
| ^t PHL | A < B or A = B | A > B | 1 | 1 | | 11 | 17 | ns |
| t _{PLH} | A = 8 | A = B | 2 | | | 13 | 20 | ns |
| ^t PHL | A = B | A = B | 2 | 1 | | 11 | 17 | ns |
| ^t PLH | A > B or A = B | A < B | 1 | | | 7 | 11 | ns |
| ^t PHL | A > B or A = B | A < B | 1 | 1 | | 11 | 17 | ns |

tpLH = propagation delay time, low-to-high-level output

NOTE 5: Load circuits and voltage waveforms are shown in Section 1.



 $^{^{\}ddagger}$ All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}$ C.

[§]Not more than one output should be shorted at a time.

tpHL = propagation delay time, high-to-low-level output

SDLS123 - MARCH 1974 - REVISED MARCH 1988

recommended operating conditions

| | S | N54LS | 35 | S | N74LS | 35 | |
|------------------------------------|-----|-------|------|------|-------|------|------|
| | MIN | NOM | MAX | MIN | NOM | MAX | UNIT |
| Supply voltage, VCC | 4.5 | 5 | 5.5 | 4.75 | 5 | 5.25 | V |
| High-level output current, IOH | | | -400 | | | -400 | μА |
| Low-level output current, IQL | | | 4 | | | 8 | mA |
| Operating free-air temperature, TA | -55 | | 125 | 0 | | 70 | °C |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | | | | | S | N54LS8 | 15 | S | N74LS8 | 15 | |
|-----|-----------------------------|---------------------|---|---|-----|--------|------|-----|------------------|------|------|
| | PARA | METER | TEST CON | IDITIONS† | MIN | TYP‡ | MAX | MIN | TYP [‡] | MAX | UNIT |
| VIH | High-level input | voltage | | | 2 | | | 2 | | | V |
| VIL | Low-level input | voltage | | | | | 0.7 | | | 0.7 | V |
| VIK | Input clamp vol | tage | VCC = MIN, | I _I = -18 mA | | | -1.5 | | | -1.5 | V |
| | High-level outpu | ut voltage | | V _{1H} = 2 V, I _{OH} = -400 μA | 2.5 | 3.4 | | 2.7 | 3.4 | | V |
| | | _ | V _{CC} = MIN, | IOL = 4 mA | | 0.25 | 0.4 | | 0.25 | 0.4 | V |
| VOL | Low-level output | it voltage | V _{IH} = 2 V, V _{IL} = V _{IL} max | 1 _{OL} = 8 mA | | | | | 0.35 | 0.5 | Ľ |
| | Input current | A < B, A > B inputs | ., | | | | 0.1 | | | 0.1 | mA |
| 11 | at maximum input voltage | all other inputs | V _{CC} = MAX, | V ₁ = 7 V | | | 0.3 | | | 0.3 | " |
| | High-level | A < B, A > B inputs | ., | V - 0.7.V | | | 20 | | | 20 | μΑ |
| ΉН | input current | all other inputs | VCC = MAX, | $V_1 = 2.7 \text{ V}$ | | | 60 | | | 60 | ۳^ |
| | Low-level | A < B, A > B inputs | 1/ - MAY | V = 0.4.V | | | -0.4 | | | -0.4 | mA |
| HL | input current | all other inputs | V _{CC} = MAX, | V ₁ = 0.4 V | | | -1.2 | | | -1.2 | |
| los | Short-circuit ou | tput current § | V _{CC} = MAX | | -20 | | -100 | -20 | | -100 | mA |
| ¹cc | Supply current | | VCC = MAX, | See Note 4 | | 10.4 | 20 | | 10.4 | 20 | mA |

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

NOTE 4: I_{CC} is measured with outputs open, A = B grounded, and all other inputs at 4.5 V.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$

| PARAMETER¶ | FROM | TO | NUMBER OF | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------|-----------------------|--------------|-------------|-------------------|----------|-----|-----|----------|
| PARAMETER | INPUT | OUTPUT | GATE LEVELS | TEST COMBITTORS | | | | |
| | | | 1 | | | 14 | | 1 |
| | | A < B, A > B | 2 | | | 19 | | ns |
| ^t PLH | Any A or B data input | | 3 | | | 24 | 36 | <u> </u> |
| | | A = B | 4 | | | 27 | 45 | |
| | | | 1 | | | 11 | | |
| | | A < B, A > B | 2 | 0 15 5 | | 15 | | ns |
| ^t PHL | Any A or B data input | | 3 | $C_L = 15 pF$ | | 20 | 30 |] " |
| | | A = B | 4 | $R_L = 2 k\Omega$ | | 23 | 45 | 1 |
| tPLH | A < B or A = B | A > B | 1 | See Note 5 | | 14 | 22 | ns |
| tPHL | A < B or A = B | A > B | 1 | 1 | | 11 | 17 | ns |
| †PLH | A = B | A = B | 2 | | | 13 | 20 | ns |
| tPHL | A = B | A = B | 2 | | | 13 | 26 | ns |
| tPLH | A > B or A = B | A < B | 1 | 1 | 13 14 | 14 | 22 | ns |
| tPHL | A > B or A = B | A < B | 1 | | | 11 | 17 | ns |

 $[\]P_{tPLH}$ = propagation delay time, low-to-high-level output

NOTE 5: Load circuits and voltage waveforms are shown in Section 1.



 $[\]ddagger$ All typical values are at V_{CC} = 5 V, T_A = 25°C. \$Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

tpHL = propagation delay time, high-to-low-level output

SN5485, SN54LS85, SN54S85 SN7485, SN74LS85, SN74S85 4-BIT MAGNITUDE COMPARATORS

SDLS123 - MARCH 1974 - REVISED MARCH 1988

recommended operating conditions

| | | SN54S8 | 5 | SN74S85 | | | UNIT |
|------------------------------------|-----|--------|-----|---------|-----|------|------|
| | MIN | NOM | MAX | MIN | NOM | MAX | UNII |
| Supply voltage, V _{CC} | 4.5 | 5 | 5.5 | 4.75 | 5 | 5.25 | V |
| High-level output current, IOH | | | -1 | | | -1 | mA |
| Low-level output current, IOL | | | 20 | | | 20 | mA |
| Operating free-air temperature, TA | -55 | | 125 | 0 | | 70 | °C |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | PARAMETER | <u> </u> | TES | ST CONDITIONS | t | MIN | TYP‡ | MAX | UNIT |
|----------|--------------------------------|---------------------|--------------------------------------|-------------------------|----------|-----|------|------|----------|
| VIH | High-level input voltage | | | | | 2 | | | V |
| VIL. | Low-level input voltage | | | | | | | 8.0 | V |
| VIK | Input clamp voltage | | VCC = MIN, | I ₁ = -18 mA | | | | -1.2 | V |
| | | | V _{CC} = MIN, | V _{IH} = 2 V, | SN54S85 | 2.5 | 3.4 | | V |
| νон | High-level output voltage | | $V_{1L} = 0.8 V$ | 1 _{OH} = -1 mA | SN74S85 | 2.7 | 3.4 | | |
| | | | VCC = MIN, | V _{IH} = 2 V, | | | | 0.5 | V |
| VOL | Low-level output voltage | | VIL = 0.8 V, | 1 _{OL} = 20 mA | | | | 0.5 | 1 |
| 11 | Input current at maximum inpu | t voltage | VCC = MAX, | V ₁ = 5.5 V | | | | 1 | mA |
| | | A < B, A > B inputs | V _{CC} = MAX | V 27 V | | | | 50 | μА |
| чн | High-level input current | all other inputs | 7 VCC - WAA | V [= 2.7 V | | | | 150 | 1 40 |
| <u> </u> | | A < B, A > B inputs | V | V. = 0 5 V | | | | -2 | mA |
| 11L | Low-level input current | all other inputs | V _{CC} = MAX, | V1 - 0.5 V | | | | -6 | 11112 |
| los | Short-circuit output current § | | V _{CC} = MAX | | | -40 | | -100 | mA |
| | | | V _{CC} = MAX, | See Note 4 | | | 73 | 115 | |
| ¹cc | Supply current | | V _{CC} = MAX, See Note 4 | T _A = 125°C, | SN54S85W | | | 110 | mA |

[†]For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

NOTE 4: I_{CC} is measured with outputs open, A = B grounded, and all other inputs at 4.5 V.

switching characteristics, VCC = 5 V, TA = 25°C

| PARAMETER¶ | FROM INPUT | TO OUTPUT | NUMBER OF GATE LEVELS | TEST CONDITIONS | MIN TYP | MAX | UNIT |
|------------------|-----------------------|--------------|--------------------------|-------------------------|---------|------|------|
| | | | 1 | | 5 | | } |
| | | A < B, A > B | 2 | | 7.5 | | ns |
| ^t PLH | Any A or B data input | | 3 | | 10.5 | 16 |] "" |
| | | A = B | 4 | | 12 | 18 | |
| | | | 1 | | 5.5 | | |
| | | A < B, A > B | 2 | 0 45 5 | 7 | | ns |
| ^t PHL | Any A or B data input | • | 3 | Cլ = 15 pF, | 11 | 16.5 | |
| | | A = B | 4 | R _L = 280 Ω, | 11 | 16.5 | |
| tPLH | A < B or A = B | A > B | 1 | See Note 5 | 5 | 7.5 | ns |
| tPHL. | A < B or A = B | A > B | 1 | | 5.5 | 8.5 | ns |
| tPLH | A = B | A = B | 2 | | 7 | 10.5 | ns |
| tPHL | A = B | A = B | 2 | | 5 | 7.5 | ns |
| tPLH | A > B or A = B | A < 8 | 1 | | 5 | 7.5 | ns |
| tPHL | A > B or A = B | A < B | 1 | | 5.5 | 8.5 | ns |

 $[\]P_{tpLH}$ = propagation delay time, low-to-high-level output

NOTE 5: Load circuits and voltage waveforms are shown in Section 1.




[‡]All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

[§]Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

tpHL = propagation delay time, high-to-low-level output

TYPICAL APPLICATION DATA





www.ti.com

11-Jan-2022

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|---------------------|-------------------------------|--------------------|--------------|--|---------|
| 5962-9754701Q2A | ACTIVE | LCCC | FK | 20 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 9754701Q2A SNJ54LS 85FK | Samples |
| 5962-9754701QEA | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9754701QE A SNJ54LS85J | Samples |
| 5962-9754701QFA | ACTIVE | CFP | W | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9754701QF A SNJ54LS85W | Samples |
| JM38510/08201BEA | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 08201BEA | Samples |
| JM38510/31101B2A | ACTIVE | LCCC | FK | 20 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101B2A | Samples |
| JM38510/31101BEA | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101BEA | Samples |
| JM38510/31101BFA | ACTIVE | CFP | W | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101BFA | Samples |
| M38510/08201BEA | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 08201BEA | Samples |
| M38510/31101B2A | ACTIVE | LCCC | FK | 20 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101B2A | Samples |
| M38510/31101BEA | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101BEA | Samples |
| M38510/31101BFA | ACTIVE | CFP | W | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 31101BFA | Samples |
| SN54LS85J | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SN54LS85J | Samples |
| SN54S85J | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SN54S85J | Samples |
| SN74LS85D | ACTIVE | SOIC | D | 16 | 40 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | LS85 | Samples |
| SN74LS85DR | ACTIVE | SOIC | D | 16 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | LS85 | Samples |

PACKAGE OPTION ADDENDUM

www.ti.com 11-Jan-2022

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|---------------------|-------------------------------|--------------------|--------------|--|---------|
| SN74LS85DRE4 | ACTIVE | SOIC | D | 16 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | LS85 | Samples |
| SN74LS85N | ACTIVE | PDIP | N | 16 | 25 | RoHS & Green | NIPDAU | N / A for Pkg Type | 0 to 70 | SN74LS85N | Samples |
| SN74LS85NSR | ACTIVE | SO | NS | 16 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | 74LS85 | Samples |
| SN74S85D | ACTIVE | SOIC | D | 16 | 40 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | S85 | Samples |
| SN74S85N | ACTIVE | PDIP | N | 16 | 25 | RoHS & Green | NIPDAU | N / A for Pkg Type | 0 to 70 | SN74S85N | Sample |
| SNJ54LS85FK | ACTIVE | LCCC | FK | 20 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 9754701Q2A SNJ54LS 85FK | Sample |
| SNJ54LS85J | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9754701QE A SNJ54LS85J | Sample |
| SNJ54LS85W | ACTIVE | CFP | W | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-9754701QF A SNJ54LS85W | Sample |
| SNJ54S85FK | ACTIVE | LCCC | FK | 20 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SNJ54S 85FK | Sample |
| SNJ54S85J | ACTIVE | CDIP | J | 16 | 1 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SNJ54S85J | Sample |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

PACKAGE OPTION ADDENDUM

www.ti.com 11-Jan-2022

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54LS85, SN54S85, SN74LS85, SN74S85:

Catalog: SN74LS85, SN74S85

Military: SN54LS85, SN54S85

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

• Military - QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 5-Jan-2022

TAPE AND REEL INFORMATION





| | Dimension designed to accommodate the component width |
|----|---|
| | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74LS85DR | SOIC | D | 16 | 2500 | 330.0 | 16.4 | 6.5 | 10.3 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74LS85NSR | SO | NS | 16 | 2000 | 330.0 | 16.4 | 8.2 | 10.5 | 2.5 | 12.0 | 16.0 | Q1 |

www.ti.com 5-Jan-2022



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LS85DR | SOIC | D | 16 | 2500 | 340.5 | 336.1 | 32.0 |
| SN74LS85NSR | SO | NS | 16 | 2000 | 853.0 | 449.0 | 35.0 |



www.ti.com 5-Jan-2022

TUBE



*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (µm) | B (mm) |
|------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-9754701Q2A | FK | LCCC | 20 | 1 | 506.98 | 12.06 | 2030 | NA |
| JM38510/31101B2A | FK | LCCC | 20 | 1 | 506.98 | 12.06 | 2030 | NA |
| M38510/31101B2A | FK | LCCC | 20 | 1 | 506.98 | 12.06 | 2030 | NA |
| SN74LS85D | D | SOIC | 16 | 40 | 507 | 8 | 3940 | 4.32 |
| SN74LS85N | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74LS85N | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74S85D | D | SOIC | 16 | 40 | 507 | 8 | 3940 | 4.32 |
| SN74S85N | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74S85N | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SNJ54LS85FK | FK | LCCC | 20 | 1 | 506.98 | 12.06 | 2030 | NA |
| SNJ54S85FK | FK | LCCC | 20 | 1 | 506.98 | 12.06 | 2030 | NA |

FK (S-CQCC-N**)

LEADLESS CERAMIC CHIP CARRIER

28 TERMINAL SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a metal lid.
- D. Falls within JEDEC MS-004



D (R-PDS0-G16)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



W (R-GDFP-F16)

CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP2-F16



14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated