

### DATA SHEET

# SKY67183-396LF: 400 to 6000 MHz Broadband Low-Noise Amplifier

### **Applications**

- FDD and TDD 4G LTE and 5G NR systems
- Active antenna array and massive MIMO
- Receive LNA for micro-cell, macro-cell, and small cell base stations
- Land mobile radios and military communications
- · Low-noise broadband gain block and driver amplifier

### **Features**

- Low-noise amplifier:
  - Very low noise figure
  - $-\,$  Temperature and process-stable active bias up to +115  $^\circ\text{C}$
  - Wide operating voltage range
  - $-\,$  Low gain slope over operating band
  - Excellent input return loss
- Integrated controller:
  - Stable amplifier bias
  - Temperature compensation
- True logic level thresholds
- Fast response time
- · Excellent broadband flat gain performance
- Minimal BOM count
- Low current IDD 56 mA @ 5 V
- Fast rise/fall time ENABLE function suitable for TDD application
- Miniature DFN (8-pin, 2 x 2 mm) package (MSL1 @ 260 °C per JEDEC J-STD-020)



Skyworks Green<sup>™</sup> products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*<sup>™</sup>, document number SQ04–0074.




Figure 1. SKY67183-396LF Block Diagram

### **Description**

The SKY67183-396LF is a wide-band low-noise amplifier with superior gain flatness and exceptional linearity.

The compact 2 x 2 mm, 8-pin Dual Flat No Lead packaged LNA is designed for FDD and TDD 4G LTE and 5G NR infrastructure systems operating from 400 to 6000 MHz.

The internal active bias circuitry provides stable performance over temperature and process variation.

A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.




Table 1. SKY67183-396LF Signal Descriptions

Pin	Name	Description		Name	Description
1	N/C	No connection (may be connected to ground with no change in performance)		EN	Enable voltage to LNA
2	RFIN	RF input (DC blocking capacitor required)		VDD	VDD voltage to LNA
3	VBIAS	Bias voltage for input gate		RFOUT	RF output. DC blocking capacitor is required.
4	RSET	External resistor to set bias current		N/C	No connection (may be connected to ground with no change in performance)

### **Electrical and Mechanical Specifications**

The absolute maximum ratings of the SKY67183-396LF are provided in Table 2. Recommended operating conditions are shown in Table 3. Thermal data is shown in Table 4.

Electrical specifications are provided in Tables 5 and 6.

#### Table 2. SKY67183-396LF Absolute Maximum Ratings<sup>1</sup>

Parameter	Symbol	Minimum	Maximum	Units
Supply voltage	Vdd		5.5	V
LNA enable	EN	-0.5	2.8	V
Quiescent supply current	Ισα		100	mA
RF input power (C/W)	Pin		+22	dBm
Storage temperature	Tstg	-40	+150	°C
Operating temperature	Та	-40	+115	°C
Junction temperature	TJ		+150	°C
Electrostatic discharge:	ESD			
Charged Device Model (CDM), Class C3 Human Body Model (HBM), Class 1A			1000 250	V V

1 Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

**ESD HANDLING**: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

### Table 3. SKY67183-396LF Recommended Operating Conditions

Parameter	Symbol	Min	Тур	Мах	Units
Supply voltage	VDD	3.3	5.0	5.25	V
LNA enable: ON	EN		0	0.63	V
OFF		1.17	1.8	2.4	V

### Table 4. SKY67183-396LF Electrical Specifications: Thermal Data<sup>1</sup>

#### **Test Condition** Parameter Symbol Min Тур Max Units Thermal resistance θJC 90 °C/W Channel temperature @ +105 °C reference ΤJ VDD = 5.25 V, IDQ = 60 mA, RF applied, dissipated power = 0.29 W°C (package heat slug) 130

#### (VDD = 5.25 V, Enable = GND, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance [Zo] = 50 $\Omega$ , Unless Otherwise Noted)

<sup>1</sup> Performance is guaranteed only under the conditions listed in this table.

### Table 5. SKY67183-396LF Electrical Specifications: 4200 to 4900 MHz Optimized BoM in Table 8<sup>1</sup>

### (VDD = 5.0 V, Enable = GND, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance [Zo] = 50 $\Omega$ , f = 4500 MHz, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
RF Specifications						
Noise figure	NF	@ 4200 MHz @ 4500 MHz @ 4900 MHz		0.5 0.5 0.6	1.0 1.0 1.1	dB dB dB
Small signal gain	IS211	@ 4200 MHz @ 4500 MHz @ 4900 MHz	16.5	18.2 18.2 17.7		dB dB dB
Input return loss	IS11I	@ 4200 MHz @ 4500 MHz @ 4900 MHz	12	16.1 32.8 21.9		dB dB dB
Output return loss	IS22I	@ 4200 MHz @ 4500 MHz @ 4900 MHz	10	11.2 23.2 14.9		dB dB dB
Reverse isolation	IS12I	@ 4200 MHz @ 4500 MHz @ 4900 MHz	26	32 32 32		dB dB dB
Third order output intercept (-20 dBm input/1 MHz tone)	0IP3	@ 4200 MHz @ 4500 MHz @ 4900 MHz	+27	+29 +29 +28.5		dBm dBm dBm
1 dB output compression point	0P1dB	@ 4200 MHz @ 4500 MHz @ 4900 MHz	+16	+20 +19 +20		dBm dBm dBm
DC Specifications						
Supply voltage	Vdd			5.0		V
Quiescent current	IDD		45	56	67	mA
Settling time 0.3 dB <sup>2</sup> Settling time 0.1 dB <sup>3</sup>	TS1 TS2	@ 4500 MHz		0.3 0.31	0.9 0.9	us us

<sup>1</sup> Performance is guaranteed only under the conditions listed in this table.

<sup>2</sup> Settling time 0.3 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.3 dB of the average steady-state "on" level.

<sup>3</sup> Settling time 0.1 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.1 dB of the average steady-state "on" level.

### Typical Performance Characteristics 4200 to 4900 MHz (VDD = 5 V, PIN = -20 dBm, Characteristic Impedance [Zo] = 50 $\Omega$ , Unless Otherwise Noted)

12




Figure 3. Small Signal Gain (dB) vs Frequency (GHz)




Figure 5. Input Return Loss (dB) vs Frequency





Figure 7. Reverse Isolation (dB) vs Frequency (GHz)








Figure 6. Output Return Loss (dB) vs Frequency




Figure 8. IIP3 (dBm) vs Frequency (GHz)




Figure 9. OIP3 (dBm) vs Frequency (GHz)




Figure 11. Small Signal Gain (dB) vs Frequency (GHz)

0

-10

-20 -30 -40 -50

-60

-70

-80

0 2 4 6 8 10 12 14 16 18 20 22 24

Reverse Isolation (dB)




Figure 10. Gain (dB) vs PIN (dBm)




Figure 12. Input Return Loss (dB) vs Frequency (GHz)






Figure 14. Output Return Loss (dB) vs Frequency (GHz)





Frequency (GHz)

Figure 13. Reverse Isolation (dB) vs Frequency (GHz)

Figure 15. Stability Factor, µ1 (dB) vs Frequency (GHz)

Figure 16. Stability Factor, µ2 (dB) vs Frequency (GHz)

Skyworks Solutions, Inc. • Phone [781] 376-3000 • Fax [781] 376-3100 • sales@skyworksinc.com • www.skyworksinc.com 204480J • Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice • March 26, 2021

-40 °C

25 °C 85 °C

115 °C

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
RF Specifications						
Noise figure	NF	@ 3400 MHz @ 3600 MHz @ 3800 MHz		0.43 0.44 0.48		dB dB dB
Gain	S21	@ 3400 MHz @ 3600 MHz @ 3800 MHz		19.2 19.1 18.9		dB dB dB
Input return loss	IS11I	@ 3400 MHz @ 3600 MHz @ 3800 MHz		15 21.3 31.2		dB dB dB
Output return loss	S22	@ 3400 MHz @ 3600 MHz @ 3800 MHz		11.6 16.3 19.9		dB dB dB
Reverse isolation	IS12I	@ 3400 MHz @ 3600 MHz @ 3800 MHz		32.9 32.4 32.1		dB dB dB
Third order output intercept point	OIP3	PIN = -20 dBm, ∆ Tone = 1 MHz: @ 3400 MHz @ 3600 MHz @ 3800 MHz		+30.4 +28.9 +34.3		dBm dBm dBm
1 dB output compression point	OP1dB	@ 3400 MHz @ 3600 MHz @ 3800 MHz		+20.2 +20.1 +20.6		dBm dBm dBm
DC Specifications				•		•
Supply voltage	Vdd			5.0		V
Quiescent current	ldd			56		mA
Settling time 0.3 $dB^2$ Settling time 0.1 $dB^3$	Ts1 Ts2	@ 3600 MHz		0.28 0.29		us us

### Table 6. SKY67183-396LF Electrical Specifications: 3400 to 3800 MHz Optimized BoM in Table 9<sup>1</sup>

(VDD = 5.0 V, Enable = GND, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance [Zo] = 50  $\Omega$ , Unless Otherwise Noted)

<sup>1</sup> Verified by characterization.

<sup>2</sup> Settling time 0.3 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.3 dB of the average steadystate "on" level.

<sup>3</sup> Settling time 0.1 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.1 dB of the average steadystate "on" level.

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
RF Specifications		·				
Noise figure	NF	@ 2300 MHz @ 2500 MHz @ 2700 MHz		0.36 0.41 0.43	0.75 0.75 0.85	dB dB dB
Gain	S21	@ 2300 MHz @ 2500 MHz @ 2700 MHz	20 20 19	21.7 21.4 20.9		dB dB dB
Input return loss	S11	@ 2300 MHz @ 2500 MHz @ 2700 MHz	9 10 10	13 16.4 18.7		dB dB dB
Output return loss	S22	@ 2300 MHz @ 2500 MHz @ 2700 MHz	7 9 9	11.2 13.5 12.6		dB dB dB
Reverse isolation	IS12I	@ 2300 MHz @ 2500 MHz @ 2700 MHz		33.8 33.4 33.2		dB dB dB
Third order output intercept point	0IP3	PIN = -20 dBm, ∆ Tone = 1 MHz: @ 2300 MHz @ 2500 MHz @ 2700 MHz	29 29 29	+32.2 +32.7 +33.4		dBm dBm dBm
1 dB output compression point	OP1dB	@ 2300 MHz @ 2500 MHz @ 2700 MHz	18 20 20	+19.5 +22 +22.1		dBm dBm dBm
DC Specifications						
Supply voltage	Vdd			5.0		V
Quiescent current	Idd			56		mA
Settling time 0.3 $dB^2$ Settling time 0.1 $dB^3$	Ts1 Ts2	@ 2500 MHz		0.3 0.33		us us

## Table 7. SKY67183-396LF Electrical Specifications: 2300 to 2700 MHz Optimized BoM in Table 101

(VDD = 5.0 V, Enable = GND, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance [Zo] = 50  $\Omega$ , Unless Otherwise Noted)

<sup>1</sup> Verified by characterization.

<sup>2</sup> Settling time 0.3 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.3 dB of the average steadystate "on" level.

<sup>3</sup> Settling time 0.1 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.1 dB of the average steadystate "on" level.

### **Typical Performance Characteristics**

2300 to 2700 MHz, (VDD = 5 V, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance (Zo) = 50  $\Omega$ , Unless Otherwise Noted)





Figure 17. Small Signal Gain (dB) vs Frequency (GHz)








Figure 21. Reverse Isolation (dB) vs Frequency (GHz)




Figure 18. Noise Figure (dB) vs Frequency (GHz)




Figure 20. Output Return Loss (dB) vs Frequency




Figure 22. IIP3 (dBm) vs Frequency (GHz)




Figure 23. OIP3 (dBm) vs Frequency (GHz)




Figure 25. Small Signal Gain (dB) vs Frequency (GHz)




Figure 27. Reverse Isolation (dB) vs Frequency (GHz)




Figure 29. Stability Factor, µ1 (dB) vs Frequency (GHz) at -40 °C




Figure 24. OP1dB (dBm) vs Frequency (GHz)




Figure 26. Input Return Loss (dB) vs Frequency (GHz)




Figure 28. Output Return Loss (dB) vs Frequency (GHz)





Figure 30. Stability Factor, µ2 (dB) vs Frequency (GHz) at -40 °C

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
RF Specifications						
		@ 1700 MHz		0.34	0.75	dB
Noise figure	NF	@ 1950 MHz		0.38	0.75	dB
		@ 2200 MHz		0.41	0.85	dB
		@ 1700 MHz	21.5	23.2		dB
Gain	IS211	@ 1950 MHz	21	22.7		dB
		@ 2200 MHz	19.5	21.5		dB
		@ 1700 MHz	10	15.7		dB
Input return loss	IS11I	@ 1950 MHz	10	26.2		dB
		@ 2200 MHz	10	14.8		dB
		@ 1700 MHz	7	9.7		dB
Output return loss	IS22I	@ 1950 MHz	10	25.2		dB
		@ 2200 MHz	10	20.6		dB
		@ 1700 MHz		34.4		dB
Reverse isolation	IS12I	@ 1950 MHz		34.2		dB
		@ 2200 MHz		34.6		dB
		$PIN = -20 \text{ dBm}, \Delta \text{ Tone} = 1 \text{ MHz}:$				
Third order output intercent point	OIP3	@ 1700 MHz	28	+31.8		dBm
Third order output intercept point	UIP3	@ 1950 MHz	28	+32.2		dBm
		@ 2200 MHz	28	+32.5		dBm
		@ 1700 MHz	17.5	+19.1		dBm
1 dB output compression point	OP1dB	@ 1950 MHz	18.0	+20.2		dBm
		@ 2200 MHz	19.0	+21.1		dBm
DC Specifications						
Supply voltage	Vdd			5		۷
Quiescent current	ldd			56		mA
Settling time 0.3 dB <sup>2</sup>	Ts1	@ 1050 MU-		0.3		us
Settling time 0.1 dB <sup>3</sup>	Ts2	@ 1950 MHz		0.33		us

### Table 8. SKY67183-396LF Electrical Specifications: 1700 to 2200 MHz Optimized BOM in Table 10<sup>1</sup> (VDD = 5.0 V. Enable = GND, TA = +25 °C, PIN = -20 dBm, Characteristic Impedance [Z0] = 50 $\Omega$ , Unless Otherwise Noted)


<sup>2</sup> Settling time 0.3 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.3 dB of the average steady state "on" level.

<sup>3</sup> Settling time 0.1 dB is measured from the time the PA enable reaches 50% of PA enable "on" level to the time at which the RF output power achieves within 0.1 dB of the average steady state "on" level.



### Typical Performance Characteristics 1700 to 2200 MHz (VDD = 5 V, PIN = -20 dBm, Characteristic Impedance [Zo] = 50 $\Omega$ , Unless Otherwise Noted

### DATA SHEET • SKY67183-396LF: 400 TO 6000 MHz BROADBAND LNA









Figure 39. Small Signal Gain (dB) vs Frequency (GHz)



22 -40°C 25°C 21 ·85°C 115°C 20 OP1dB (dBm) 19 18 17 16 1.7 1.8 1.9 2 2.1 2.2 Frequency (GHz)






Figure 40. Input Return Loss (dB) vs Frequency (GHz)




Figure 42. Output Return Loss (dB) vs Frequency (GHz)




Figure 43. Stability Factor,  $\mu$ 1 (dB) vs Frequency (GHz) at -40 °C

### **Evaluation Board Description**

The SKY67183-396LF Evaluation Board is used to test the performance of the SKY67183-396LF LNA. An Evaluation Board schematic diagram is shown below. Bill of Materials (BOMs) for

Evaluation Boards optimized for 4200 to 4900 MHz, 3400 to 3800, 2300 to 2700 MHz, and 1700 to 2200 MHz appear in the following pages. An EVB assembly diagram is shown in Figure 46, layer details appear in Figure 47.




Figure 45. SKY67183-396LF Evaluation Board Schematic

Component	Value	Size	Part Number
C1	1.8 pF	0402	GJM1555C1H1R8BB01D
C2	0.8 nH	03015	LQW04AN0N8C00D
C3	0.4 pF	0402	GJM1555C1HR40WB01D
C4	DNI		
C5	DNI		
C6	DNI		
C7	4.7 uF	0402	GRM155C80J475MEAAD
C8	2.2 pF	0402	GRM1555C1H2R2BA01D
C9	0 Ω	0402	Not critical
C10	1.0 nH	0402	LQG15HS1N0S02D
C11	DNI		
C12	DNI		
L1	18 nH	0402	LQW15AN18NG8ZD
L2	6.2 nH	0402	LQG15HS6N2S02D
R1	8.2 kΩ	0201	Not critical
R2	DNI		
R4	100 Ω	0201	Not critical

Component	Value	Size	Part Number
C1	1.8 pF	0402	GJM1555C1H1R8BB01
C2	1.8 nH	0402	LQW15AN1N8C00
C3	0.4 pF	0402	GJM1555C1HR40WB01D
C4	DNI		
C5	DNI		
C6	DNI		
C7	4.7 uF	0402	GRM155C80J475MEAAD
C8	5.6 pF	0402	GRM1555C1H5R6BA01D
C9	0 Ω	0402	Not critical
C10	1.8 nH	0402	LQG15HS1N8S02D
C11	DNI		
C12	DNI		
L1	12 nH	0402	LQW15AN12NG8ZD
L2	5.6 nH	0402	LQG15HS5N6S02D
R1	8.2 kΩ	0201	Not critical
R2	DNI		
R4	100 Ω	0201	Not critical

### Table 10. SKY67183-396LFEK2 Evaluation Board Bill of Materials (BOM) for 3400 to 3800 MHz Tuning

### Table 11. SKY67183-396LFEK3 Evaluation Board Bill of Materials (BOM) for 2300 to 2700 MHz Tuning

Component	Value	Size	Part Number
C1	5.0 pF	0402	GJM1555C1H5R0BB01D
C2	2.7 nH	0402	LQW15AN2N7B8ZD
C3	0.4 pF	0402	GJM1555C1HR40WB01D
C4	10 pF	0402	GRM1555C1H100JA01D
C5	DNI		
C6	DNI		
C7	4.7 uF	0402	GRM155C80J475MEAAD
C8	22 pF	0402	GRM1555C1H220JA01
C9	1.8 pF	0402	GRM1555C1H1R8BA01D
C10	3.3 nH	0402	LQG15HS3N3S02D
C11	DNI		
C12	DNI		
L1	22 nH	0402	LQW15AN22NG8ZD
L2	5.6 nH	0402	LQG15HS5N6S02D
R1	8.2 kΩ	0201	Not critical
R2	DNI		
R4	100 Ω	0201	Not critical

Component	Value	Size	Part Number
C1	5.0 pF	0402	GJM1555C1H5R0BB01D
C2	4.7 nH	0402	LQW15AN4N7B8ZD
C3	0.4 pF	0402	GJM1555C1HR40WB01D
C4	15 pF	0402	GRM1555C1H150JA01D
C5	DNI		
C6	DNI		
C7	4.7 uF	0402	GRM155C80J475MEAAD
C8	22 pF	0402	GRM1555C1H220JA01
C9	1.8 pF	0402	GRM1555C1H1R8BA01D
C10	6.2 nH	0402	LQG15HS6N2S02D
C11	300 Ohm	0402	ERJ-2RKF3000C
C12	DNI		
L1	22 nH	0402	LQW15AN22NG8ZD
L2	5.6 nH	0402	LQG15HS5N6S02D
R1	8.2 KOhm	0201	ERJ-1GNF8201C
R2	DNI		
R4	100 Ohm	0201	ERJ-1GNF1000C

Table 12. SKY67183-396LFEK4 Evaluation Board Bill of Materials (BOM) for 1700 to 2200 MHz Tuning




Figure 46. SKY67183-396LF EVB Assembly Diagram

		тот	AL THICKNESS	1.578mm	TOL: +/- 10%
S=N/A	CPW = N/A		BMASK	0.020mm	SOLDER RESIST
S=N/A			∟4	0.047mm	FINISHED Cu.
W=N/A	W=N/A	CORE	DIELECTRIC	0.254mm	FR4 (4.34)
			L3	0.018mm	Cu-0.5oz.
		PREPREG	DIELECTRIC	0.900mm	FR4 (4.34)
			L2	0.018mm	Cu-0.5oz.
5=0.100mm	CPW = 0.375mm	CORE	DIELECTRIC	0.254mm	R04350B
S=0.100mm			L1	0.047mm	FINISHED Cu.
W=0.301mm	TOL: +/-5% W=0.508mm		TMASK	0.020mm	SOLDER RESIST
50-OHM TRACE	50-OHM TRACE	CROSS SECTION	NAME	THICKNESS	MATERIALS

Figure 47. SKY67183-396LF EVB Layer Details

204480-019

### **Package Dimensions**


Typical part marking for the SKY67183-396LF is shown in Figure 48, PCB layout footprint is provided in Figure 49. Package dimensions are shown in Figure 50. Tape and reel dimensions are shown in Figure 51.

### **Package and Handling Information**


Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY67183-396LF is rated to Moisture Sensitivity Level 1 (MSL1) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to the Skyworks Application Note, *Solder Reflow Information*, document number 200164.


Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.











Notes:

1. All measurements are in millimeters.

2. Dimensions and tolerances according to ASME Y14.5M-1994.


3. Coplanarity applies to the exposed heat sink ground pad as well as the terminals.

4. Plating requirement per source control drawing (SCD) 2504.

5. Dimension applies to metallized terminal and is measured between 0.15 mm and 0.30 mm from terminal tip.



204480-022



6. Ao and Bo measurement point to be 0.30 mm from bottom pocket.
7. All measurements are in millimeters.

### Figure 51. SKY67183-396LF Tape and Reel Dimensions

### **Ordering Information**

Part Number	Product Description	Evaluation Board Part Number	
	400 to 6000 MHz Broadband Low-Noise Amplifier	SKY67183-396EK1 (4.2 to 4.9 GHz Tuning)	
		SKY67183-396EK2 (3.4 to 3.8 GHz Tuning)	
SKY67183-396LF		SKY67183-396EK3 (2.3 to 2.7 GHz Tuning)	
		SKY67183-396EK4 (1.7 to 2.2 GHz Tuning)	

Copyright © 2021 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.